

Aufschraubschlauchtüllen



Gewinde	LW	SW	Messing	Messing vernickelt	Edelstahl 1.4571	Edelstahl 1.4408
G 1/8	4 mm	14 mm	MS239A1804	MSN239A1804	-	-
G 1/8	6 mm	14 mm	MS239A1806	MSN239A1806	239.10-ES	-
G 1/8	8 mm	14 mm	MS239A1808	MSN239A1808	239.11-ES	-
G 1/8	9 mm	14 mm	MS239A1809	MSN239A1809	-	-
G 1/8	10 mm	14 mm	MS239A1810	MSN239A1810	-	-
G 1/4	4 mm	17 mm	MS239A1404	MSN239A1404	-	-
G 1/4	6 mm	17 mm	MS239A1406	MSN239A1406	239.12-ES	-
G 1/4	8 mm	17 mm	MS239A1408	MSN239A1408	239.13-ES	-
G 1/4	9 mm	17 mm	MS239A1409	MSN239A1409	-	-
G 1/4	10 mm	17 mm	MS239A1410	MSN239A1410	239.14-ES	-
G 1/4	12 mm	17 mm	MS239A1412	MSN239A1412	-	-
G 1/4	13 mm	17 mm	MS239A1413	MSN239A1413	239.15-ES	-
G 3/8	4 mm	19 mm	MS239A3804	MSN239A3804	-	-
G 3/8	6 mm	19 mm	MS239A3806	MSN239A3806	239.18-ES	-
G 3/8	8 mm	19 mm	MS239A3808	MSN239A3808	239.19-ES	-
G 3/8	9 mm	19 mm	MS239A3809	MSN239A3809	-	-
G 3/8	10 mm	19 mm	MS239A3810	MSN239A3810	239.20-ES	-
G 3/8	12 mm	19 mm	MS239A3812	MSN239A3812	-	-
G 3/8	13 mm	19 mm	MS239A3813	MSN239A3813	239.21-ES	-
G 1/2	6 mm	24 mm	MS239A1206	MSN239A1206	239.25-ES	-
G 1/2	8 mm	24 mm	MS239A1208	MSN239A1208	239.26-ES	-
G 1/2	9 mm	24 mm	MS239A1209	MSN239A1209	-	-
G 1/2	10 mm	24 mm	MS239A1210	MSN239A1210	239.27-ES	-
G 1/2	12 mm	24 mm	MS239A1212	MSN239A1212	-	-
G 1/2	13 mm	24 mm	MS239A1213	MSN239A1213	239.28-ES	-
G 1/2	16 mm	24 mm	MS239A1216	MSN239A1216	-	-
G 1/2	19 mm	24 mm	MS239A1219	MSN239A1219	-	-
G 3/4	9 mm	32 mm	MS239A3409	MSN239A3409	-	-
G 3/4	13 mm	32 mm	MS239A3413	MSN239A3413	-	-
G 3/4	16 mm	32 mm	MS239A3416	MSN239A3416	-	-
G 3/4	19 mm	32 mm	MS239A3419	MSN239A3419	-	-
G 3/4	25 mm	32 mm	MS239A3425	MSN239A3425	-	-
G 1	19 mm	38 mm	MS239A119	MSN239A119	-	-
G 1	25 mm	38 mm	MS239A125	MSN239A125	-	-
G 1	32 mm	38 mm	MS239A132	MSN239A132	-	-
G 1 1/4	32 mm	50 mm	MS239A11432	MSN239A11432	-	-
G 1 1/4	38 mm	50 mm	MS239A11438	MSN239A11438	-	-
G 1 1/2	32 mm	55 mm	MS239A11232	MSN239A11232	-	-
G 1 1/2	38 mm	55 mm	MS239A11238	MSN239A11238	-	-
G 1 1/2	50 mm	55 mm	MS239A11250	MSN239A11250	-	-
G 2	50 mm	70 mm	MS239A250	MSN239A250	-	-