



## Product Specifications

	Cell Type	18650 Li-ion battery cell
	Cell Model	Samsung SDI ICR18650-26H
	Typical Capacity	13000mAh at 0.2C
	Output Parameters	USB1 output, 5V/2.1A (Max) USB2 output, 5V/1.0A (Max)
	Charging Parameters	Input voltage 5V±5% Input current 1.5A(MAX) 1#
	Sleep Current	200uA ±5%
	Weight	290g ±10g
	Operating Temperature:	
	Discharge	-20°C to 60°C
	Charge	0°C to 45°C
Storage	1 year : -20~25°C(1*) 3 months : -20~45°C(1*) 1 month: -20~60°C(1*)	
Storage humidity range:	Less than 75% RH	
<b>Scope of delivery:</b> AccuPower PB_13000 Power Bank USB cable with Micro USB connector Adapter Micro-USB to Apple Lightning (iPhone 5, 5C, 5S, etc.)		

1#: the charge current will be 1.5A, The PCBA micro USB input pin's voltage must larger than 4.75V, 1.5A



### Care and safety recommendations:

Never open, short circuit or put in fire. Do not install backwards. Avoid short circuit with metal objects.

### ATTENTION:

Improper handling may result in fire, personal injury or product failure due to leakage or Explosion. Use only the charger specified for this battery type. Improper use will reduce considerably the battery life. Please pay attention to following recommendations:

1. Always avoid Deep discharge of the battery
2. Charge the battery before longer Storage.
3. Use only the battery charger specified for this battery type.
4. Do not leave battery in charger over 24 hours.
5. Keep it in a cool and dry place.
6. Avoid exposure to high temperatures.
7. Do not disassemble or modify the battery, may cause the battery to generate heat, explode or ignite.
8. Dispose properly used batteries. Contact your city recycling coordinator. Thank you.