



REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT DATE




5.08X(N-1)+16.4

5.08X(N-1)+10.8



5.08X(N-1)



Pollution degree	2	2	3
Overvoltage category	II	III	III
Rate impulse voltage(KV)	4.0K	4.0KV	4.0KV
Rate voltage(V)	630V	320V	250V
Rate current(A)	12A		


1. Rated voltage/current : 300V / 15A
 2. Withstanding voltage : AC1600V/1Min.
 3. Torque value : M3.0 , 5.31lb.in
 4. Wire range : 28~12AWG
 IEC Standard

NOTES1:

- 1. Dimension shall be interpreted per ASME Y14.5-2009
- 2. Pitch : 5.08mm, Poles : N=02~24P
- 3. Stripping length : 7~8mm
- 4. Operating temperature: -40°C~+105°C
- 5. Undimensioned tolerances:

Pitch range in mm	Over	Over	Nominal dimension range in mm	Over	Over	Over
TO	6	10	TO	30	60	100
TO	10	24	TO	60	100	150
TO	10	24	TO	60	100	150
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00
±1.30	±2.0					


6. RoHS Compliance



16.90

5.00

2EDG-DB - 5.08 - XXP - 1Y - 00A (H)
 (Series No.) (Pitch) (Poles) (Single Pitch) (Color) : 1.(Grey)
 2.(Blue)
 3.(Black)
 4.(Green)
 5.(Orange)
 6.(Red)
 7.(Transparent)
 8.(Yellow)
 9.(White)



Drill Hole Layer

5.08X(N-1)+10.8

∅5.20

∅3.20

PART NO.:	/	NAME:	NINGBO DEGSON ELECTRICAL CO., LTD	
APPD:	/	CHKD:	/	
DRFT:	/	TITLE:	CUSTOMER DRAWING	

2EDG-DB-5.08-XXP-1Y-00A(H)

DRAWING NO.:	/	REV	DO
SHEET	1/1	SHEET	1/1
SCALE	1:1	SCALE	1:1