


TBS partnumber : SP-DSR-010

### COILED CABLE MEASUREMENTS



### CABLE SPECIFICATION

Cable type : LiF12Y-2D-11Y 8x0,14 mm<sup>2</sup> TB20 FLEX, 37x0,07 mm bare copper wires  
 Conductor insulation : TPE-E  
 Conductor colours : according to DIN 47100  
 Shielding : white+brown cores separately shielded by a lap  
 Overall sheath : PUR Colour : black  
 Temperature range : +25 °C to +70 °C  
 Weight : ± 0,10 kg/pc

#### Tolerances ± 10% unless stated otherwise

In all cases in which we act as offeror or supplier, our offers, assignments given to us and agreements concluded with us are subject to the METAALUNIE TERMS AND CONDITIONS. These terms and conditions have been filed at the Registry of the Rotterdam District Court.

The Best Solution  
 De Slof 2 5107 RJ Dongen  
 The Netherlands  
 V.A.T.-nr.: NL 815889215B01

HR Eindhoven nr.: 18048791  
 Rabobank Tilburg nr.: 1255.77.397  
 IBAN code : NL 12 RABO 0125577397  
 BIC code : RABONL2U

Phone : +31 (0) 162 523 436  
 Fax : +31 (0) 162 519 993  
 E-mail : sales@the-best-solution.com  
 Internet : www.the-best-solution.com