

Passive 1X/10X Voltage Probe

▶ P2220



▶ P2220.

P2220 Passive Voltage Probe

The P2220 200-MHz Passive Voltage Probe permits selection of 1X or 10X attenuation, using a switch located on the probe head.

This probe is compatible with TDS200, TDS1000, TDS2000, and TPS2000 Series oscilloscopes. The P2220 probe also provides floating measurement capability up to 30 V_{RMS} with TPS2000 Series oscilloscopes only. **(Note:** Do not float with TDS2000, TDS1000 or TDS200 Series oscilloscopes.)

▶ Features & Benefits

- 1X/10X Attenuation
- 200 MHz Bandwidth
- 1.5 Meter Length
- UL3111-1, CSA1010.1, EN61010-1, EN61010-2-031 and IEC61010-2-031

▶ Applications

- Relative Low Frequency Measurements
- Low Frequency Computer and Telecom Measurements
- Power Supplies
- Low Frequency Amplifiers

COMPUTING

COMMUNICATIONS

VIDEO

P2220 Passive Voltage Probe

▶ P2220

▶ Characteristics

X10 Position

Bandwidth – DC: 200 MHz.

Probe Length – 1.5 m.

Attenuation Ratio – 10:1.

Compensation Range – 15 to 25 pF.

Input Capacitance – 17.0 pF.

Input Resistance – 10 MΩ.

Maximum Input Voltage – 300 V CAT II.

Maximum Voltage Between Reference Lead and Earth Ground – $30 V_{RMS}^{*1}$.

X1 Position

Bandwidth – DC: 6 MHz.

Probe Length – 1.5 m.

Attenuation Ratio – 1:1.

Compensation Range – All scopes with 1 MΩ input.

Input Capacitance – 110 pF.

Input Resistance – 1 MΩ.

Maximum Input Voltage – 150 V CAT II.

Maximum Voltage Between Reference Lead and Earth Ground – $30 V_{RMS}^{*1}$.

*1 The float voltage must be subtracted from the tip to earth ground voltage. For example, if the reference lead is floated to $30 V_{RMS}$, the tip voltage to the reference lead is limited to $270 V_{RMS}$.

▶ Ordering Information

P2220

1X/10X, 200 MHz Passive Voltage Probe.

Includes: Retractable hook tip (013-0318-00), 6 in. ground lead (196-3466-02), Adjustment tool (003-1873-00), Marker band set (016-1315-00), Instruction manual (071-1464-00).

Contact Tektronix:

ASEAN / Australasia / Pakistan (65) 6356 3900

Austria +43 2236 8092 262

Belgium +32 (2) 715 89 70

Brazil & South America 55 (11) 3741-8360

Canada 1 (800) 661-5625

Central Europe & Greece +43 2236 8092 301

Denmark +45 44 850 700

Finland +358 (9) 4783 400

France & North Africa +33 (0) 1 69 86 80 34

Germany +49 (221) 94 77 400

Hong Kong (852) 2585-6688

India (91) 80-22275577

Italy +39 (02) 25086 1

Japan 81 (3) 6714-3010

Mexico, Central America & Caribbean 52 (55) 56666-333

The Netherlands +31 (0) 23 569 5555

Norway +47 22 07 07 00

People's Republic of China 86 (10) 6235 1230

Poland +48 (0) 22 521 53 40

Republic of Korea 82 (2) 528-5299

Russia, CIS & The Baltics +358 (9) 4783 400

South Africa +27 11 254 8360

Spain +34 (91) 372 6055

Sweden +46 8 477 6503/4

Taiwan 886 (2) 2722-9622

United Kingdom & Eire +44 (0) 1344 392400

USA 1 (800) 426-2200

USA (Export Sales) 1 (503) 627-1916

For other areas contact Tektronix, Inc. at: 1 (503) 627-7111

Last Update March 01, 2004

Our most up-to-date product information is available at:
www.tektronix.com



Copyright © 2004, Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks or registered trademarks of their respective companies.

07/04 HB/WOW

51W-17984-0