


### Data sheet

#### Durable Type K & T Exposed Welded Tip Thermocouples (ANSI Colour Code)



- Thermocouple types K & T to ANSI MC96.1
- Fast response, welded exposed junction
- 1 or 2 metre long Teflon® PFA insulated twin-twisted lead
- Durable construction with choice of conductor size, 1/0.2, 1/0.3mm solid or 7/0.2mm stranded
- Class 1 cable specification in accordance with BS EN 60584-3:2008
- Tolerance to ANSI MC96.1 Class 1
- Miniature plug termination
- Temperature range -75°C to +250°C
- Ideal for test & development applications

Thermocouple type	Outer Colour	Conductors	Length	Order code
Type K	Yellow	1/0.2	1m	XE-3583-001
Type K	Yellow	1/0.2	2m	XE-3581-001
Type K	Yellow	1/0.3	1m	XE-3580-001
Type K	Yellow	1/0.3	2m	XE-3582-001
Type K	Yellow	7/0.2	1m	XE-3584-001
Type K	Yellow	7/0.2	2m	XE-3585-001
Type T	Blue	1/0.3	1m	XE-3589-001
Type T	Blue	1/0.3	2m	XE-3587-001