


## AS-Interface control cabinet module

SmartLine25 4DI 3DO T C AUX



- 1 addressing socket  
2 COMBICON connector with screw terminals optional



## Electrical data

Operating voltage [V]	26.5...31.6 DC
Max. current consumption from AS-i [mA]	50
Max. current load total [A]	3; (> 50 °C: 2000 mA)
Integrated watchdog	yes

## Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4; Number of digital outputs: 3
------------------------------	---

## Inputs

Number of digital inputs	4
Input circuit of digital inputs	PNP
Sensor supply of the inputs	external (E+/E-), to PELV
Voltage supply [V]	18...30
Max. total current rating of inputs [mA]	200
Input current High [mA]	6...10
Input current Low [mA]	0...2
Min. switching level high signal [V]	11
Digital inputs protected against short circuits	yes

# AC2266



## AS-Interface control cabinet module

SmartLine25 4DI 3DO T C AUX

Outputs							
Number of digital outputs				3			
Circuit				PNP			
Voltage range DC [V]	20...30; (external (E+/E-), to PELV)						
Max. current load per output [mA]	1000; (utilisation category DC-12: 700 mA; utilisation category DC-13 (control of electromagnets): 20 W (IEC 60947-5-1))						
Short-circuit proof	yes						
Electrically separated	yes						
Operating conditions							
Ambient temperature [°C]	-20...70						
Note on ambient temperature	cRUus: -25...60 °C						
Protection	IP 20						
Tests / approvals							
EMC	EN 50295						
MTTF [years]	187						
AS-i classification							
AS-i version	3.0						
AS-i addressing	addressing socket						
Extended addressing mode possible	yes						
AS-i profile	S-7.A.E						
AS-i I/O configuration [hex]	7						
AS-i ID code [hex]	A.E						
AS-i certificate pending	yes						
Assignment of the data bits	data bit	D0	D1	D2	D3		
	input	I-1	I-2	I-3	I-4		
	Output	O-1	O-2	O-3	-		
Mechanical data							
Weight [g]	139						
Type of mounting	mounting on DIN rail; string mounting possible						
Materials	PA						
Displays / operating elements							
Display	switching status	LED, yellow					
	operation	LED, green					
	errors	LED, red					
Accessories							
Accessories (optional)	COMBICON connectors						
Remarks							
Pack quantity	1 pcs.						

# AC2266



## AS-Interface control cabinet module

SmartLine25 4DI 3DO T C AUX

### Electrical connection

COMBICON:

### Connection

I-	I-	I-	I-
I1	I2	I3	I4
I+	I+	I+	I+

O-	O-	O-	O-
O1	O2	O3	
A+	A-	E+	E-

A+	AS-i +
A-	AS-i -
I+	Sensor supply +24V
I-	Sensor supply 0V
E+	external voltage supply for sensors/actuators
E-	external voltage supply for sensors/actuators
I1...I4	switching input sensor 1...4
O1...O3	switching output actuator 1...3
O-	switching output actuator 0V