

M12 FEMALE 0° SHIELDED, B CODED ,INTERBUS

PUR 3x2x0.25 shielded violet 25m


M12

Female straight



Interbus, B-coded

5-pole, shielded

Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Female



Product may differ from Image

Approvals



Form

14261

Technical Data

| | |
|-------------------------------|---|
| Operating voltage | 60 V AC/DC |
| Operating current per contact | max. 4 A |
| Locking of ports | Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing |

Cables

| | |
|-----------------------------|------------------------|
| Cable number | 799 |
| No./diameter of wires | 3 × 2 × (AWG 24) |
| Wire isolation | PE (br,wh,gr,pk,gn,ye) |
| C-track properties | 2 Mio. |
| Jacket Color | violet |
| Shore hardness outer jacket | 85 ± 5A |
| Material (jacket) | PUR |
| Outer diameter | approx. 7.7 mm |

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

| | |
|----------------------------|--------------|
| Bend radius (fixed) | 10 × outer Ø |
| Bend radius (moving) | 15 × outer Ø |
| Temperature range (fixed) | -40...+70 °C |
| Temperature range (mobile) | -20...+50 °C |
| Shielded | yes |

Commercial data

| | |
|------------------------|----------|
| country of origin | DE |
| customs tariff number | 85444290 |
| minimum order quantity | 1 |