

RS422 TO RS232 CONVERTER, MALE, MALE, 9-PIN FOR SCREW CONNECTION TO RS422 INTERFACE, 180 DGR CABLE OUTLET, FOR CONNECTION OF THIRD-PARTY PLC



Product type designation

Installation type/mounting

Wall mounting/direct mounting possible	Yes; Can be screwed onto the HMI
--	----------------------------------

Interfaces

Number of pins HMI-side	9; Pin (RS422)
Number of pins device-side	9; Pin (RS232)

Standards, approvals, certificates

CE mark	Yes
---------	-----

Ambient conditions

Ambient temperature in operation

- | | |
|--------|-------|
| • Min. | 0 °C |
| • max. | 55 °C |

Storage/transport temperature

- | | |
|--------|--------|
| • Min. | -20 °C |
| • max. | 70 °C |

Relative humidity

- | | |
|-------------------|------|
| • Operation, max. | 95 % |
|-------------------|------|

Mechanics/material

Screw type	
• 4.5 V	Yes; HMI page
Type of housing (front)	
• plastic	Yes

Dimensions	
Width	31 mm
Height	50 mm
Thickness	11 mm

Weights	
Without packaging	26 g

Scope of supply	
Delivery unit in items	1

other	
Note:	suitable for all SIMATIC HMI RS422 interfaces, for details refer to the operating instructions of the respective device

Usable in the following products	
• Product 1	6AV6642-0*
• Product 2	6AV6542-0*
• Product 3	6AV6545-0*
• Product 4	6AV6644-*
• Product 5	6AV6545-8*
• Product 6	6AV6640-0C*
• Product 7	6AV6643-7BA00-*
• Product 8	6AV6643-7CD00-*
• Product 9	6AV6643-7DD00-*
• Product 10	6av2124-0*
• Product 11	6av2124-1*
• Product 12	6AV2124-2*
• Product 13	6AV6647-0*
• Product 14	6AV6643-8*
• Product 15	6AV2123-2*

last modified: 12.03.2015