

SIMATIC DP, CONNECTING MODULE FOR PROFINET
 INTERFACE MODULES ET 200PRO IM 154-3 PN HF, M12 7/8" S, 2
 X M12 AND 2 X 7/8"

Input current	
from supply voltage 1L+, max.	No current input, only infeed current, max. 8 A
from load voltage 2L+ (without load), max.	No current input, only infeed current, max. 8 A

Interfaces	
PROFINET IO	
• Transmission rate, max.	100 Mbit/s; full-duplex, PROFINET

Accessories	
Function description	IM PN; 2xM12 2x7/8" interface module, power supply from 1L+ and 2L+ max. per 8 A, internal transfer 2L+ max. 8 A, 1L+ max. 5 A
belongs to product	ET 200pro; IM154-3 PN HF

Dimensions	
Width	60 mm
Height	130 mm
Depth	51 mm

last modified: 10/13/2017