

SIVACON sicube, roof, EMC, IP40, W: 600 mm, D: 500 mm, galvanized



Figure similar

Model	
Product brand name	SIVACON
Product designation	Roof
Design of the surface	galvanized
Design of the product / EMC version	Yes
Protection class	
Protection class IP	IP40
Suitability	
Suitability for use / for outside use	No
Product details	
Product component	
• cable entry	No
• ventilation	No
Mechanical Design	
Width	600 mm
Depth	500 mm

Material	steel		
Equipment marking	<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 • acc. to DIN EN 81346-2 		
EMC	Declaration of Conformity	Test Certificates	other

[Miscellaneous](#)



[Special Test Certificate](#)

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1065-2UD12-0A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1065-2UD12-0A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1065-2UD12-0A

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



