



## Two Point Pull Handles

### Series #RG

- Two-Point or Pull Handle and pocket handle varieties available in phenolic, thermoplastic and thermoplastic overmold materials.
- Female insert, tapped thread, pocket and plain molded hole options are available.
- New! Soft touch handle is available in 6 standard colors: black, white, red, orange, gray, and yellow.
- Click on the part number for additional information and search by diameter, mounting, material, etc.
- Colors available upon request.



ITEM#	DIAMETER A	HEIGHT B	CENTERS D	MATERIAL TYPE	MOUNTING DIAMETER	MOUNTING TYPE	THREAD LENGTH/
							DEPTH
RG-1N.100.09	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1N.100.84	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1N.120.09	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1N.120.84	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1N.140.09	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1N.140.84	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1N.160.09	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1N.160.84	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1N.180.09	218	58	180	Thermoplastic	M10	Thru-Hole	1.57
RG-1N.180.84	218	58	180	Thermoplastic	M10	Thru-Hole	1.57
RG-1P.100.09	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1P.100.84	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1P.120.09	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1P.120.84	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1P.140.09	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1P.140.84	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1P.160.09	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1P.160.84	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1P.180.09	218	58	180	Thermoplastic	M10	Thru-Hole	1.57
RG-1P.180.84	218	58	180	Thermoplastic	M10	Thru-Hole	1.57
RG-1S.100.09	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1S.100.84	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1S.120.09	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1S.120.84	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1S.140.09	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1S.140.84	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1S.160.09	194	52	160	Thermoplastic	M8	Thru-Hole	1.375

RG-1S.160.84	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1S.180.09	218	58	180	Thermoplastic	M10	Thru-Hole	1.57
RG-1S.180.84	218	58	180	Thermoplastic	M10	Thru-Hole	1.57