


Myriad Adjustable Square - White with Silver bezel

MYRIAD ADJ SQUARE WHITE 4000K PHDIM SILVER BEZ
2056230



Product features

- The Myriad Adjustable Square recessed spotlight is a high efficient accent downlight, fixture color RAL 9016 - Traffic white / Bezel, correlated colour temperature of 4000K, color rendering index Ra107, fixture lumen 684lm, total power consumption 10W, luminaire efficacy 68 lm/W, nominal light beam angle 24°, mains voltage 230-240V~ AC, control technology type: leading edge/trailing edge phase dim, product length 76mm, width 76mm, height 115mm, cut-out dimension 72x72mm, IP rating IP20, 5 years warranty.



PRODUCT OVERVIEW

Product name	MYRIAD ADJ SQUARE WHITE 4000K PHDIM SILVER BEZ
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Office, Residential & Consumer, Retail
ETIM Class	EC001744
Warranty	5 years
Fixture luminous flux (lm)	684
Luminaire efficacy (lm/W)	68
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	24
Photobiological Risk Group	RG1
Total power consumption (W)	10
Electrical protection	Class II
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5025768562305

DATA TABLE

General data

Product name	MYRIAD ADJ SQUARE WHITE 4000K PHDIM SILVER BEZ
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Office, Residential & Consumer, Retail

Myriad Adjustable Square - White with Silver bezel

MYRIAD ADJ SQUARE WHITE 4000K PHDIM SILVER BEZ
2056230

Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
Warranty	5 years

Optical data

Fixture luminous flux (lm)	684
Luminaire efficacy (lm/W)	68
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Adjustable chromaticity	N
Beam Angle (°)	24
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	10
Mains voltage (V)	230-240V
Electrical protection	Class II
Transformer required	Yes
Drive current (mA)	250
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	68500

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Nominal Product Width (mm)	76
Nominal Product Height (mm)	115
Weight (kg)	0.38
Recessed Depth (mm)	115

Packaging

Single packaging type	Carton
Product EAN number	5025768562305
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
DUN14 (outer)	05025768562305
Units per outer package	1

Myriad Adjustable Square - White with Silver bezel MYRIAD ADJ SQUARE WHITE 4000K PHDIM SILVER BEZ 2056230


Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

PHOTOMETRY


0.5	0.23	E(0°) E(C0)	12208 5701
1.0	0.46	E(0°) E(C0)	3052 1425
1.5	0.69	E(0°) E(C0)	1388 633
2.0	0.92	E(0°) E(C0)	763 358
2.5	1.15	E(0°) E(C0)	458 228
3.0	1.37	E(0°) E(C0)	339 156

Distance [m] Cone diameter [m] Illuminance [lx]

— C0 - C180 (Half beam angle: 25.5°)



TECHNICAL DRAWINGS



Dimensions (mm)