

## Electronic 3-point quick internal micrometer

From dia. 12.5 mm, IP67



### Application:

For measuring through holes and blind bores (from Ø 12.5 mm) and short centring shoulders in series.

### Execution:

- Self-centring and self-aligning
- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force
- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Max./min. value memory
- HOLD function
- Preset function
- Tolerance function

### Advantage:

- Pistol grip for quick measurements using retractable lever

### Delivery:

Single device with battery (1 x 3 V lithium type CR 2032) and calibration certificate in a case



<b>Art. no.</b>	<b>31919 012</b>
<b>Brand</b>	SYLVAC
<b>Manufacturer Part Number</b>	954.6014
<b>Min./max. length measuring range</b>	12.5-16 mm
<b>Measuring depth</b>	62 mm
<b>Data transmission type</b>	Bluetooth/Proximity
<b>Digit increment</b>	0.001 mm
<b>IP protection class</b>	IP 67
<b>Error limit</b>	4 µm
<b>Display</b>	Digital
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	3V CR2032 Lithium
<b>DIN</b>	863
<b>Gross Weight</b>	1.650 kg
<b>Product Group</b>	317

### EAN

7640125710793