

Shelf boltless rack, single-row

Zinc-plated



Application:

Universal shelving system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools

Execution:

- Shelves height-adjustable in increments of 25 mm for variable adaptation to stored goods
- Shelves with a 50 mm hole grid to accommodate accessories, shelf edge height 40 mm
- For technical reasons, depth reinforcements are always zinc plated, even with coated frames
- Basic rack planning dimensions: Nominal length + 56 mm, nominal depth + 36 mm
- With dismantled or pre-assembled frame

Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



Art. no.	50167 643
Brand	META
Manufacturer Part Number	2001429 1
Height	2500 mm
Length	1306 mm
Depth	436 mm
Nominal length	1300 mm
Nominal depth	400 mm
Design	Add-on shelving
Type of assembly	To insert
Surface	Zinc plated
Design of the frame	Pre-assembled
Grid dimension	25 mm
Number of shelves	5 PCS
Load-carrying capacity per shelf	230 kg
Load-carrying capacity per field	2350 kg
Number of frame	1 PCS
Quality label	RAL-RG 614/ 1
Made in	Germany
Gross Weight	34.280 kg
Product Group	508

EAN

4026212011050