



	REVISED	DR	APP



NOTE:

1. Electrical properties:
 - 1.1 Tested by quantum data 980 handhold test instrument for DP1.4(32.4G)
 - 1.2 Tested by PC,3840*2160 120Hz 4:4:4 8bit HDR OFF
 Tested by PC,3840*2160 120Hz 4:2:2 12bit HDR ON
 Tested by PC,3840*2160 60Hz 4:4:4 12bit HDR ON
 Tested by PC,720P,1080P
2. ROHS 2.0 and REACH

MODEL LIST

Model	Length	DSP
	500mm	4K120Hz 4:4:4 8bit
10-70025	1000mm	4K120Hz 4:4:4 8bit
	1500mm	4K120Hz 4:4:4 8bit
	1800mm	4K120Hz 4:4:4 8bit
10-70035	2000mm	4K120Hz 4:4:4 8bit
10-70045	3000mm	4K120Hz 4:4:4 8bit
10-70055	5000mm	4K120Hz 4:4:4 8bit

CABLE	(1/0.32B*1P+D+AL+HM)*5C+1/0.32B*4C+ADB16/10/0.12AL+AM+PVC OD:7.0±0.1MM COLOR:BLACK
SHELL	BLACK ABS
INNER MOLD	LD-PE
CONNECTOR	DP1.4 MALE ,(RED) GOLD PLATED PIN,GOLD PLATED SHELL



DESCRIPTION		DP PLUG - DP PLUG (1.4) 8K					
SIZE	A4	DATE	21.01.2019	CHECKED		TOL	
UNIT	MM	DRAWN	R.Hueller	APPROVED			BS10-70025
CUSTOM TARIF NO.: 854442909000							