

**Cable glands
VP 16-K54**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Type	VP 16-K54
Order No.	0295060000
Version	Cable glands, Blanking plug, Polyamid 6 (PA6 - GF30), RAL 7035, PG 16, IP 54
GTIN (EAN)	4008190170479
Qty.	100 pc(s).

Cable glands VP 16-K54

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	10 mm	Net weight	1.8 g
--------	-------	------------	-------

General information

Cable gland	PG	Colour code	RAL 7035
DIN	DIN 46320 (for PG thread)	External thread	PG 16
Head diameter	27 mm	Length of thread	5 mm
Material	Polyamid 6 (PA6 - GF30)	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Protection degree with GWDR	IP 65
UL 94 flammability rating	V-2		

Classifications

ETIM 3.0	EC000032	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-10	eClass 6.2	27-14-91-10
eClass 7.1	27-14-91-10		

Product information

Descriptive text ordering data	Other versions available on request. The sealing plugs must be tightened "hand-tight" with the screwdriver.
Descriptive text technical data	Optional sealing ring

Approvals

ROHS	Conform
------	---------