


Pressure gauge, series K

The following data is valid for all pressure gauges



MA15VK-359EN

Technical Data

Port	centre back entry, brass with PTFE-ring (NPT-thread without PTFE-ring)
Case	Black plastic
Window	Clear plastic
Instrument dial	White plastic
Indicator	Black plastic
Measuring system	Bourdon tube Cu Sn8
Movement	Combination brass / POM
Operating temperature range EN 837-1	-20 °C to +60 °C
Scale	Double scale MPa (red), bar (blue) incl. SMC logo
Accuracy class	2.5

Order reference

Part number	Pressure range		Connection thread	A	B	C	D
	bar	MPa					
K8-2.5-40	0 – 2.5	0 – 0.25	G1/8	39	25	10	41
K8-10-40	0 – 10	0 – 1.0	G1/8	39	25	10	41
K8-16-40	0 – 16	0 – 1.6	G1/8	39	25	10	41
K8-2.5-50	0 – 2.5	0 – 0.25	G1/8	50	25.5	10	41.5
K8-4-50	0 – 4	0 – 0.4	G1/8	50	25.5	10	41.5
K8-6-50	0 – 6	0 – 0.6	G1/8	50	25.5	10	41.5
K8-10-50	0 – 10	0 – 1.0	G1/8	50	25.5	10	41.5
K4-10-40	0 – 10	0 – 1.0	G1/4	39	25	10	41
K4-2.5-50	0 – 2.5	0 – 0.25	G1/4	50	25.5	10	41.5
K4-4-50	0 – 4	0 – 0.4	G1/4	50	25.5	10	41.5
K4-6-50	0 – 6	0 – 0.6	G1/4	50	25.5	10	41.5
K4-10-50	0 – 10	0 – 1.0	G1/4	50	25.5	10	41.5
K4-16-50	0 – 16	0 – 1.6	G1/4	50	25.5	10	41.5
K4-2.5-50 NPT	0 – 2.5	0 – 0.25	1/4 NPT	50	25.5	10	41.5
K4-4-50 NPT	0 – 4	0 – 0.4	1/4 NPT	50	25.5	10	41.5
K4-6-50 NPT	0 – 6	0 – 0.6	1/4 NPT	50	25.5	10	41.5
K4-10-50 NPT	0 – 10	0 – 1.0	1/4 NPT	50	25.5	10	41.5