

## Bracket

MULTI-MOUNT-20(45x75)  
Order Number: 70112511

Main Parameters (*)	min	typ	max	Unit
Operating Temperature	-20		50	°C
Storage Temperature	-50		70	°C

### Technical Parameters

RoHS yes

### Mechanical Parameters

Size	Ø45x75 mm
Material	aluminium
Housing Color	black
Weight	132.5 g

### Mount Parameter

Total Height (h1)	75 mm
Height to Laseraxis (h2)	60 mm
Height of Base (h3)	25 mm
Mount Diameter (d1)	Ø 20 mm
Diameter of Base (d2)	Ø 45 mm
Width of Mount (b)	26 mm
Height of Mount (g)	50 mm
Height of Mount Head (k)	50 mm
Depth of Mount (t)	15 mm
Angle of Rotation Alpha ( $\alpha$ )	360 °
Angle of Rotation Beta ( $\beta$ )	$\pm 90$ °


(\*) Over the complete operating temperature range

## Features




- Anodized aluminium
- Very robust
- For industrial applications

## Picture



## Safety Label



## Valid Revision

1 | 22-APR-2021