

Coaxial Cable Connector 11_N-50-2-2/133_N

Description

Straight cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 11 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | soldered |
| Outer contact | clamped |
| Weight | 0.0367 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|-----------------------|-----------------------------------|
| Centre contact | Brass | Gold Plating (Nickel underplated) |
| Outer contact | Brass | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |
| Coupling nut | Brass | SUCOPLATE (R) Plating |
| Gasket | VMQ (Silicone rubber) | |
| Fastening nut | Brass | SUCOPLATE (R) Plating |
| Crimp ferrule | Brass | SUCOPLATE (R) Plating |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00006957 |
| Catalogue drawing | DOU-00006959 |
| Assembly instruction | DOC-0000177464 |

Ordering Information

| | |
|----------------|--------------------|
| Single package | 11_N-50-2-2/133_NE |
|----------------|--------------------|

Additional Information

| | |
|-----------------|--|
| Suitable cables | K_02252_D, ENVIROFLEX_316_D, G_02232_D |
|-----------------|--|