

infinitely adjustable clamp, complete



Application:

For clamping workpieces. It is designed to withstand extremely high loads and is particularly suitable for clamping cutting tools and punches.

Version:

- made of steel, forged, tempered and galvanised.

Advantage:

- The infinitely variable adjustable clamp quickly spans various clamping heights without any additional support and requires little space on the machine table.



Art. no.	26223 020
For table grooves according to DIN 650	14 mm
Min./max. clamping height	0-50 mm
Clamping shoe length	140 mm
Clamping shoe width	50 mm
Bore diameter	17 mm
Distance 2	60 mm
Distance	30 mm
Distance 1	55 mm
Slot nut width of clamping screw	14 mm

EAN-Code

4020772074913