


META CLIP S3 inclined shelving rack

Load capacity per bay 200 kg, zinc plated



Execution:

- Add-on rack, for extending the basic rack
- FIFO principle (First In/First Out): The products stored first are used first (particularly important for goods with expiry dates)
- The uppermost level is fully available for loading since there are no crossbraces
- The shelves have an 18° incline so that stored goods will automatically slide towards the front for removal
- The shelves have no protruding edges in the direction of the incline
- Low front stop side for easy removal of boxes and crates
- Shelves adjustable in increments of 25 mm
- Lateral guide available on request
- Basic rack planning dimensions: Nominal length + 56 mm, frame depth 1,228 mm (overall)



Art. no.	50164 801
Brand	META
Manufacturer Part Number	20091075
Height	2000 mm
Length	1056 mm
Depth	1228 mm
Nominal length	1000 mm
Nominal depth	1228 mm
Type of shelving	Add-on shelving
Design	One side
Type of assembly	To insert
Surface	Zinc plated
ESD-capable	No
Design of the frame	Disassembled
Grid dimension	25 mm
Number of shelves	4 PCS
Load-carrying capacity per shelf	200 kg
Load-carrying capacity per field	1200 kg
Number of frame	1 PCS
Made in	Germany
Gross Weight	69.173 kg
Product Group	508

EAN

4026212238167