


## Blacklight BL368 Toughcoat T12

*F20W T12 BL368 24 Toughcoat™*  
0000125



### Product features

- Excellent fragment retention in the event of breakageThe protective FEP coating meets the IEC60068-2-75 Pendulum Hammer test (5 Joule) and the 4m drop test, demonstrating excellent glass retention in the event of accidental lamp breakageThe 97% UV-A transmission of FEP maintains maximum insect attraction



## PRODUCT OVERVIEW

Product name	F20W T12 BL368 24 Toughcoat™
Technology	Special applications
Lamp shape	Tubular shape
Type	T12
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	SPG
ETIM Class	EC002962
E-number FI	4940431
Light colour	BL368 Blacklight
Wattage (W)	20.00
Dimmable	No
Average life (Nominal) (h)	10000
Product EAN number	5410288001258

## DATA TABLE

### General data

Product name	F20W T12 BL368 24 Toughcoat™
Technology	Special applications
Lamp shape	Tubular shape
Type	T12
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	SPG
Operating temperature range (°C)	-20°C - 40°C
ETIM Class	EC002962
E-number FI	4940431

### Optical data

## Blacklight BL368 Toughcoat T12 *F20W T12 BL368 24 Toughcoat™* 0000125

Ambient temperature for maximum luminous flux (°C)	25
Light colour	BL368 Blacklight
Adjustable chromaticity	N

### Electrical data

Wattage (W)	20.00
Watt (Rated) - High frequency (W)	13.50
Mains voltage (V)	230-240V
Control gear required	Yes
Transformer required	No
Dimmable	No

### Lifetime data

Average life (Nominal) (h)	10000
----------------------------	-------

### Physical data

Nominal Product Length (mm)	600.0
Nominal Product Diameter (mm)	38
Max. Length base to base (mm) - A	589.8
Length base to pin Min-Max (mm) - B	594.5-596.9
Max. Lamp Length (mm) - C/L	604.0
Max. Lamp Diameter (mm) - D	40.5
Weight (kg)	0.201

### Packaging

Single packaging type	Carton
Product EAN number	5410288001258
Packaging single length / height (cm)	60.3
Packaging single width (cm)	4.3
Packaging single depth (cm)	4.1
DUN14 (outer)	15410288001255
Units per outer package	25
Packaging outer length / height (cm)	63.0
Packaging outer width (cm)	22.0
Packaging outer depth (cm)	21.0

### Safety data

Lamp mercury content (mg)	9.00
Optimal operating condition (°C)	-20-40
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes
Intended purpose	Flykilling - Insect attraction
Suitable for household illumination	No
Safety message	Not suitable for household

## Blacklight BL368 Toughcoat T12 *F20W T12 BL368 24 Toughcoat™* 0000125

### PHOTOMETRY

---

