



Goobay

High Speed HDMI™ cable with Ethernet, gold-plated

HDMI™ male (type A) > HDMI™ male (type A)

- 3D support with a resolution up to 1080p
- HDCP conform
- supports more color spaces as DSC and sYCC601
- 4 times higher resolutions as 1080p (max. 4096x2160 at 60Hz)



0.50 m	69124	Bulk	3.00 m	31894	Bulk
1.00 m	31891	Bulk	5.00 m	31895	Bulk
1.50 m	31892	Bulk	10.00 m *	31896	Bulk
2.00 m	31893	Bulk	15.00 m *	31898	Bulk



Goobay

High Speed HDMI™ cable with Ethernet, gold-plated

HDMI™ male (type A) > HDMI™ male (type A)

- with 2 ferrites
- 3D support with a resolution up to 1080p
- HDCP conform
- supports more color spaces as DSC and sYCC601
- 4 times higher resolutions as 1080p (max. 4096x2160 at 60Hz)



1.00 m	31906	Bulk	5.00 m	31910	Bulk
1.50 m	31907	Bulk	10.00 m*	31911	Bulk
2.00 m	31908	Bulk	15.00 m*	31912	Bulk
3.00 m	31909	Bulk			



Goobay

High Speed HDMI™ cable with Ethernet, gold-plated

HDMI™ male (type A) > HDMI™ male (type A)

- with high-quality cotton sheath
- 3D support with a resolution up to 1080p
- HDCP conform
- supports more color spaces as DSC and sYCC601
- 4 times higher resolutions as 1080p (max. 4096x2160 at 24Hz)



1.00 m	63804	Bulk
1.50 m	63805	Bulk
2.00 m	63806	Bulk
3.00 m	63807	Bulk



* Official test criteria exist for High Speed HDMI™ specifications cables only up to 7.5 m.