



Permit Control Station with Slimview Group Lock Box

Key Characteristics	Article Number	152730
	Order Reference	KIT,SLIMVIEW RED,PERMIT DISPLAY STATION
	Total Qty per Pack	1 Piece(s) / Piece
	Application(s)	Lockout tagout
	Quantity	1
	Brand	Brady®
	Trade Name	SlimView
	Country of Origin	CN
	Holds Number of Documents/Papers	25

Dimensions	Size - Width (mm)	266.70 mm
	Size - Height (mm)	590.55 mm
	Size - Depth (mm)	79.38 mm
	Max. Shackle Diameter (mm)	8.38 mm
	Dimensions	266,70 mm (W) x 590,55 mm (H) x 79,38 mm (D)
	Holds Document Size	210.00 x 297.00 mm (A4)

Material Characteristics	Brady Material Type	Steel
	Colour	Red
	Max. Service Temp. °C	120 °C
	Min. Service Temp. °C	-40 °C

Product Features	Max number of padlocks attached	12
	Max. Number of Padlocks Stored	12
	# of Holes	12
	Lockout Station Filled or Unfilled	Unfilled

What's Included	Includes	(1) Permit Display Case - 151736, (1) SlimView Lock Box - 150505
-----------------	----------	--

Compliance	UNSPSC	39121904
	RoHS Compliance Status	Not applicable to this product
	REACH SVHC Status	Part does not contain an SVHC
	REACH Candidate List Date	17 January 2022
	Approval/Compliance	OSHA 1910.147