


24566-447 EUROPACPRO SIDE PANEL FOR TEXTILE GASKET, TYPE H, HEAVY, HANDLE HOLES, 6 U, 235 MM





Combinations of horizontal rails and side panels



KEY FEATURES

For high mechanical demands, 19" bracket, tox-cold welded, Al, 2-mm, clear passivated, front anodized

Versions for EMC textile gasket

PRODUCT ATTRIBUTES

Product Type: Side Panel

Product Family: EuropacPRO

Туре: Туре Н

Rack Height: 6 U

Board Depth: 235 mm

Package Quantity: 2

Depth: 235 mm

ADDITIONAL PRODUCT DETAILS

Side Panel, Type H, with handle holes, tox welded to the 19" bracket for textile gasket.

Side panel and 19" bracket are tox-cold welded together. tox = Clinching technique, without add aids. This takes place with special tools and high pressure.

Please order front handles separately.

9 U version available on request.



North America

All locations +1.763.422.2661 Chat with us: schroff.nvent.com

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: schroff.nvent.com

nVent.com

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: schroff.nvent.com

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: schroff.nvent.com



© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

Our powerful portfolio of brands:

nVent reserves the right to change specifications without notice.