

Timing Control Made Easy

7954 and 7957 Multi-function time relays

Versatile and easy to program



Programmable DIN Rail Time Relay



Trumeter's new range of digital time relays offer 8 or 18 operating modes, easily configured on the 3 digit LCD display: a wide range of 0.1s - 999Hr to suit all applications; a clear indication of the relay status via the front panel LED; can accept a wide range of operating voltages for most installations. The keylock feature means settings cannot be tampered with, for 100% reliable operation.




Key Features

Features

- Compact 17.5mm wide DIN rail mountable
- 3 digit LCD for easy programming and run time indication
- Tamper proof with key lock feature
- Wide timing range: 0.1s 999Hr
- Multi-function: 8 (7954) or 18 (7957) selectable operating modes
- Universal Voltage: 24 240VAC/VDC
- · Option to select up/down timing
- · CE, UL & cUL approved
- 8 AMP Form C (SPDT) Relay outputs

Programmable:



- Preset Time: The Timer Duration selected by the user
- Run Time: In Down counting ▼ mode it indicates the time remaining, while in Up counting \(^{\text{a}}\) mode indicates the elapsed time.
- Default Mode: Down counting
- Up/Down ✓ blinks during the Timer Duration (T)

Specifications:

- Input voltage range
- Relay Capability
- Temp range
- Time ranges

Part Numbers

7954 8 Functions 7957 18 Functions


Operating modes


7957

- ON Delay
- Repeat Cycle OFF/ON
- Repeat Cycle ON/OFF
- Impulse on Power Up
- · Accumulative Delay on Signal
- Accumulative Delay on Inverted Signal
- · Accumulative Impulse on Signal
- Signal ON Delay
- Inverted Signal ON Delay
- Signal OFF Delay
- Impulse ON/OFF
- Signal OFF/ON
- Leading Edge Impulse 1
- Leading Edge Impulse 2
- Trailing Edge Impulse 1
- · Trailing Edge Impulse 2
- Delayed Impulse
- Inverted Signal ON Delay (Type 2)


7954

- ON Delay
- Repeat Cycle OFF/ON
- Repeat Cycle ON/OFF
- Signal ON/OFF
- Signal OFF Delay
- Interval
- Signal OFF/ON
- · One Shot Output





Easy To Program & Install



Full specifications available online www.trumeter.com



Pilot Mill, Alfred Street Bury, Lancashire BL9 9EF Tel: +44 161 674 0960 Email: sales.uk@trumeter.com

North America Office

Trumeter 702 S. Military Trail Deerfield Beach, Florida FL 33442, USA Tel: +1 954 725 6699 Email: sales.usa@trumeter.com

Innovative Design Technologies Sdn. Bhd Lot 5881, Lorong Iks Bukit Minyak 1 Taman Perindustrian Iks, 14000 Bukit Tengah Penang, Malaysia Web: www.idtworld.com Tel: + 604 5015700 Email: info@idtworld.com