



Part no.: 50081461
KD 095-5A-PG9
Connector



Figure can vary

Contents

- Technical data
- Electrical connection

Part no.: 50081461 – KD 095-5A-PG9 – Connector

Technical data

Electrical data

Performance data

Operating voltage	Max. 125 V AC/DC
Rated operating current	4,000 mA

Connection

Connection 1

Type of connection	Connector with screw terminals
Thread size	M12
Type	Female
Material	Metal
Handle body material	Plastic
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

Cable properties

Permissible conductor cross section	0.14 ... 0.75 mm ²
-------------------------------------	-------------------------------

Mechanical data

Design	Cylindrical
Dimension (Ø x L)	20 mm x 52.5 mm

Environmental data

Ambient temperature, operation	-25 ... 85 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	85369010
eCl@ss 8.0	27069190
eCl@ss 9.0	27069190
ETIM 5.0	EC001578
ETIM 6.0	EC001578

Electrical connection

Connection 1	
Function	
Type of connection	Connector with screw terminals
Thread size	M12
Type	Female
Material	Metal
Handle body material	Plastic
No. of pins	5 -pin
Encoding	A-coded

Part no.: 50081461 – KD 095-5A-PG9 – Connector

Connection 1	
Design	Axial

Pin	Pin assignment
1	V+
2	Signal 1
3	V-
4	Signal 2
5	FE/SHIELD

