

## MEN POWER SUPPLY 1/2-PHASE, SMOOTHED

IN: 230/400+/-15VAC OUT: :24V/2,5ADC

Current: 2.5 A


Output rating: 60 W


with MES DIN-rail adapter

This power supply units meet the (EN 61000-3-2) standard for harmonic current.

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Approvals



### Input

Input voltage	230/400 ±15 V AC
Input current	0.5 A (230 V AC); 28 A (400 V AC)
Input fuse (external)	0.8 A (T) (230 V AC); 5 A (T) (400 V AC)
Frequency	50...60 Hz

### General data

Standards	(EN 61558-2-6), (EN 62041 category I), (EN 55011 B), (EN 61000-3-2)
Mounting method	DIN-rail mountable TH35-15 (EN 60715) or for key-hole mounting
Dimensions H × W × D	83×84×124 mm
Fixing centers a × b × c	65.5×64×4.8 mm
Temperature range	-20...+60 °C, no condensation

### Output

Output voltage	24 V DC (SELV)
Output current (Ta 60/40 °C)	max. 2.5 A (230 V AC); 3 A (400 V AC)
Ripple	max. 5 %rms
Output fuse	7.5 A (automotive fuse FKS)
Output filter	LED, VDR and smoothing capacitor

### Commercial data

country of origin	CZ
customs tariff number	85044090
minimum order quantity	1