

Ultrasonic transit time Sensor Clamp-On, Universal Size C3, pair, dedicated, Ex Zone 0,1,2, Class 1, Div 1,2, any pipe materials, Liquid, Pipe Diameter range 51 - 305 mm (2 - 12"), Temperature -40C - +121C (-40F - +250F) Housing Polyetherimide/StSt corrosion resistant, for FST020, FST030, (substitute for FUx1010)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.de/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>