

SIVACON sicube, roof, IP55, W: 400 mm, D: 400 mm, galvanized



Figure similar

Model	
Product brand name	SIVACON
Product designation	Roof
Design of the surface	galvanized
Design of the product / EMC version	No
Protection class	
Protection class IP	IP55
Suitability	
Suitability for use / for outside use	No
Product details	
Product component	
• cable entry	No
• ventilation	No
Mechanical Design	
Width	400 mm
Depth	400 mm

<b>Material</b>	steel		
<b>Equipment marking</b>	<ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> <li>• acc. to DIN EN 81346-2</li> </ul>		
<b>EMC</b>	<b>Declaration of Conformity</b>	<b>Test Certificates</b>	<b>other</b>

[Miscellaneous](#)



EG-Konf.

[Special Test Certificate](#)

[Miscellaneous](#)

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1044-2UD11-0A>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1044-2UD11-0A>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF1044-2UD11-0A](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1044-2UD11-0A)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



