



3W

VT-803 3W-WALL LAMP WITH BRIDGELUX CHIP COLORCODE:4000K
 BLACK BODY

Lumens 300	Beam Angle 120	Dimensions 220x80x200mm
----------------------	--------------------------	-----------------------------------

Day White
 SKU:8347




Technical Information

Watts: 3	Dimmable: No
Lumens: 300	Warranty (Years): 2
On/Off Cycles: 15000	PF: >0.5
Beam Angle: 120	CRI: >80
Unit Color: Black	Operation Temperature: -20 to +45°C
Body Type: Iron	Input Power: AC:110-240V,50/60Hz
Long life: 30,000 Hours	Sensor Compatibility: Yes
IP Rating: IP20	

Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.781
Unit CBM	0.004232

Listing Details

EAN Code	3800157633031
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	160

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES