



Sample photo

Order symbol: ALN 123608
Product nbr: 7811250
Description: Enclosure
Remarks: Aluminium

EAN: 6418074011404
EI. number:
Finland: 3420050
Electric No. Sweden: 7811250

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	362	125	81	AM 1222	Mounting plate
inch:	14.3	4.9	3.2	AM 1236	Mounting plate
Materials:				ARH 12	DIN-35 Mounting rail
Material:	Aluminium			ARH 36	DIN-35 Mounting rail
Base colour:	RAL 7001			MR 75005	Selftapping taptite screw M5
Cover screws material:	Stainless steel			MRS 28541	Wall fastening lug (2 pcs)
Cover colour:	RAL 7001			PH A & AH A/B	Hinge set
Gasket material:	Polyurethane			Rating:	
Temperatures:				Ingress Protection (EN 60529): IP66/IP67/IP68	
Temperature °C (short term):	-50 ... 140 °C			Impact Resistance (EN 62262): IK08	
Temperature °C (continuous):	-50 ... 80 °C			NEMA Class: NEMA 1, 4, 4X, 12, 13	
Temperature °F (short term):	-60 ... 285 °F			Certificates:	
Temperature °F (continuous):	-60 ... 175 °F			SGS Fimko	
Accessories:				AM 1212	
				Mounting plate	

