

collet chuck DIN 6343 173 E, round

ORION[®]

Execution:

- hardened and ground
- clamping bridge max. 0.1 mm of the nominal diameter
- Concentricity
- \varnothing 1-10 mm \leq 20 μ m
- \varnothing 11-30 mm \leq 30 μ m
- \varnothing 31-60 mm \leq 40 μ m
- up to \varnothing 8 mm smooth bore, from \varnothing 9 mm with crosswise grooves
- Other designs and complete sets can be supplied on request.



Art. no.	23353 060
Brand	ORION
Manufacturer Part Number	23353060
Outer diameter	60 mm
Diameter	48 mm
Length	94 mm
Clamping diameter	6 mm
Profile shape	Round and smooth
DIN	173
Diameter 2	48 mm
Gross Weight	0.657 kg
Product Group	2AE

EAN

4053625355020