

Hydraulic pressure cylinder RSM (flat)



Execution:

- Single-acting cylinder.
- Extra flat.
- With spring return and scraper ring
- Operating pressure of 700 bar.
- Bronzed piston rod.

Advantage:

- Retaining ring prevents piston rod from being pushed out.

Delivery:

1x ENERPAC hydraulic pressure cylinder RSM 50.



Art. no.	29521 100
Brand	ENERPAC
Manufacturer Part Number	RSM1000
Model	RSM 1000
Max. compressive force	887 kN
Lift height	16 mm
Oil capacity	203 cm ³
Construction height, retracted	85 mm
Housing outer diameter	178 mm
Diameter of hydraulic piston	153 mm
Weight	14.5 kg
Gross Weight	14.000 kg
Product Group	258