

## Micrometer

With flat measuring faces and deep throat

Mitutoyo

### Application:

For measuring e.g. sheet thickness

### Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Spherical anvil and flat spindle
- Friction coupling for consistent, repeatable measuring force

### Advantage:

- Micrometer with deep throat

### Delivery:

Including box, adjustment wrench, setting standard (from 25 mm)



<b>Art. no.</b>	<b>32016 468</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	118-102
<b>Min./max. length measuring range</b>	0-25 mm
<b>Vernier scale</b>	0.01 mm
<b>Measuring surface diameter</b>	6.3 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Bracket depth</b>	160 mm
<b>Spindle clamping</b>	Yes
<b>Error limit</b>	4 µm
<b>Display</b>	Nonius
<b>Type</b>	A – flat/flat
<b>Min./max. measurement force</b>	3-8 N
<b>Calibration Group</b>	D
<b>Gross Weight</b>	1.325 kg
<b>Product Group</b>	3MA

### EAN

4946368011820