

electronic pocket vernier calipers

Digital ABS AOS callipers with carbide-tipped measuring surfaces

Mitutoyo

Application:

For measuring hard materials.

Execution:

- ON/OFF
- Zero setting at any position
- Digimatic
- ABSOLUTE system for reliable measurement
- 9 mm LCD display
- High-contrast display

Advantage:

- Carbide-tipped measuring faces
- AOS (advanced on-site sensor) magnetic-inductive scale

Delivery:

Delivered in box



Art. no.	32018 001
Brand	MITUTOYO
Manufacturer Part Number	500-235-30
Min./max. length measuring range	0-200 mm
Data transmission type	DIGIMATIC
Depth gauge rod	Flat
With drive wheel	No
Error limit	0.02 mm
Length of jaw	50 mm
Design	Metric
Digit height	9 mm
Length of cross tips	24.5 mm
Digit increment	0.01 mm
Type of locating	With locking screw
Preset function	No
With mm / inch switching	No
Length	290 mm
With automatic shut off	No
Battery designation	1,5 V SR44
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.002 kg
Battery voltage	1.55 V
Type of rechargeable battery/battery	Silver oxide
Calibration Group	A
ISO	13385-1
Functions	Absolute function, Origin (Dimension preset), Reset (Zeroing the display), On/Off
Gross Weight	0.565 kg
Product Group	3MA

EAN

4946368668017