

## Platform trolley series 500 with 2 front walls, zinc plated

Loading area made of MDF board, load capacity 500 kg



### Execution:

- Galvanised
- Loading area, longitudinal walls 400 mm high, made of melamine-coated MDF board
- Loading area height 260 mm
- Push handle made of 25 mm steel tubing
- 2 fixed castors and 2 castors made of solid rubber 200 x 50 mm
- The 500 series also includes table trolleys, cabinet trolleys, platform trolleys with front walls and other variants.



<b>Art. no.</b>	<b>50250 022</b>
<b>Brand</b>	KONGAMEK
<b>Manufacturer Part Number</b>	KM533-2
<b>Type</b>	With front and rear wall
<b>Load-carrying capacity</b>	500 kg
<b>Length</b>	1000 mm
<b>Width</b>	700 mm
<b>Height</b>	900 mm
<b>Loading surface length</b>	1000 mm
<b>Loading surface size</b>	1000 x 700 mm
<b>Loading-surface width</b>	700 mm
<b>Material of loading surface</b>	Medium density fibreboard
<b>Colour</b>	Silver coloured
<b>Surface</b>	Zinc plated
<b>Number of steering rollers</b>	2
<b>Number of fixed rollers</b>	2
<b>With wheel lock</b>	No
<b>Wheel diameter</b>	200 mm
<b>Material of wheel</b>	Solid rubber
<b>Made in</b>	Sweden
<b>Gross Weight</b>	31.000 kg
<b>Product Group</b>	5AT

### EAN

7350050352103