

digital current clamp multimeters

TRUE RMS

BENNING

Application:

Micro-amp measuring range for testing
flame sensors and sacrificial anodes
on heating systems/reservoirs

Execution:

- Data logger, memory function, Bluetooth®
- App for downloading, saving and sharing measured values via smartphone/tablet
- INRUSH for measuring switch-on currents (motors etc.)
- Low-pass filter for measurements of clocked motor drives
- Frequency/capacitance measurement
- functions: AutoV, LoZ, Volt sensor, ZERO

Delivery:

Includes Accessories: bag, batteries, measuring leads



Art. no.	75024 401
Brand	BENNING
Manufacturer Part Number	044688
Model	CM 10-1
Display range	6000 digits
Measuring accuracy	+/- 2 %
Min./max. test voltage (DC)	0.1 mV/DC-1000 V/DC
Min./max. test voltage (AC)	0.1 V/AC-1000 V/AC
Min./max. alternating current of measuring range	10 mA-1500 A
Min./max. direct current of measuring range	10 mA-1500 A
Continuity testing	Yes
Diode testing	Yes
Min./max. electrical-resistance measuring range	0.1 Ohm-600 kOhm
Min./max. frequency	0.00001 / 10 kHz
Volt sensor	Yes
Max. collet opening	42 mm
Memory function	HOLD, MAX/MIN, INRUSH, ZERO
Measuring procedure	TRUE RMS
Overvoltage protection category	CAT III/1000 V, CAT IV/600 V
Length x width x height	245 x 85 x 48 mm
Gross Weight	0.750 kg
Product Group	7AH

EAN

4014651446885