


REV	DESCRIPTION	DATE
Δ	R1K-97063	SEP 2008/08/25
Δ	R1E-100163	SEP 2011/01/17



NOTE:

1. MAXIMUM ELECTRIC CURRENT : $\frac{A/WG}{AMP} \frac{18}{17}$
2. MAXIMUM ELECTRICAL RATING : 105°C 600 VOLTS MAX.
3. INSULATION MATERIAL : NYLON
4. INSULATION COLOR :
 FRENCH COLOR : RED , Δ ORANGE
 GERMAN COLOR : YELLOW
 DIN COLOR : RED
5. CONNECTOR MATERIAL : COPPER TUBE.
6. WIRE RANGE : 2#18 A/WG(2#18 mm²)
7. CONNECTOR SURFACE TREATMENT : TIN PLATED

Tolerance Unless Otherwise Specified	
mm	mm
0 - 0.25	±0.05
0.25 - 1	±0.10
1 - 3	±0.15
3 - 10	±0.20
10 - 30	±0.30
30 - 100	±0.50
100 - 300	±1.00
300 - 1000	±2.00

NAME			UNIT	
WMT NO	TE1008	WDRN	-----	MMXMC
NUMBER	SCALE	SHEET	PAGE	DDED
DATE	2007/07/26	4/1	1-2	10F1
				DRAWN

RS stock # 184-9660

