











CHAIN TERMINAL

SRB series (With insulation grip) <Made in Belgium>



 Listed file No. E42024 DIN 46225 (except *-marked items)

Model No.	Standard	Applicable wire			Material	Finish	Dimensions(mm)					Q'ty / reel
		mm ²	AWG #	Insulation O.D. (mm)			W	L	E	d (dia.)	Material thickness	
SRB-1.0-M3		0.5 to 1.0	20 to 18	2.0 to 3.3	Brass	—	8.0	21.0	17.0	3.2	0.6	5,000
SRB-1.0T-M3						Tin-plated						
SRB-1.0-M3-W9.5 *						—						
SRB-1.0T-M3-W9.5 *	Tin-plated											
SRB-2.5-M3		1.0 to 2.5	18 to 14	2.7 to 4.3	Brass	—	8.0	21.0				
SRB-2.5T-M3						Tin-plated						
SRB-2.5-M3-W9.5 *						—						
SRB-2.5T-M3-W9.5 *	Tin-plated											
SRB-1.0-M4		0.5 to 1.0	20 to 18	2.0 to 3.3	Brass	—	8.0	21.0				
SRB-1.0T-M4						Tin-plated						
SRB-1.0-M4-W9.5 *						—						
SRB-1.0T-M4-W9.5 *	Tin-plated											
SRB-2.5-M4		1.0 to 2.5	18 to 14	2.7 to 4.3	Brass	—	8.0	21.0				
SRB-2.5T-M4						Tin-plated						
SRB-2.5-M4-W9.5 *						—						
SRB-2.5T-M4-W9.5 *	Tin-plated											
SRB-1.0-M5-W8 *		0.5 to 1.0	20 to 18	2.0 to 3.3	Brass	—	8.0	21.0				
SRB-1.0T-M5-W8 *						Tin-plated						
SRB-1.0-M5						—						
SRB-1.0T-M5	Tin-plated											
SRB-2.5-M5-W8 *		1.0 to 2.5	18 to 14	2.7 to 4.3	Brass	—	8.0	21.0				
SRB-2.5T-M5-W8 *						Tin-plated						
SRB-2.5-M5						—						
SRB-2.5T-M5	Tin-plated											
SRB-1.0-M6 *		0.5 to 1.0	20 to 18	2.0 to 3.3	Brass	—	9.5	21.75	5.3	0.6	4,000	
SRB-1.0T-M6 *						Tin-plated						
SRB-2.5-M6 *		1.0 to 2.5	18 to 14	2.7 to 4.3	Brass	—	9.5	21.75				
SRB-2.5T-M6 *						Tin-plated						

RoHS compliance

Crimping machine, Applicator

Contact	Crimping machine	Applicator		
		Crimp applicator	Dies	Crimp applicator with dies
SRB-1.0(T)-M3/4	AP-K2N	MK-L	MK/SRB-1.0-W8	APLMK SRB10-W8
SRB-1.0(T)-M5-W8			MK/SRB-1.0-W8	APLMK SRB10-W8
SRB-1.0(T)-M3/4-W9.5			MK/SRB-1.0-W9.5	APLMK SRB10-W9.5
SRB-1.0(T)-M5/6			MK/SRB-1.0-W9.5	APLMK SRB10-W9.5
SRB-2.5(T)-M3/4			MK/SRB-2.5-W8	APLMK SRB25-W8
SRB-2.5(T)-M5-W8			MK/SRB-2.5-W8	APLMK SRB25-W8
SRB-2.5(T)-M3/4-W9.5			MK/SRB-2.5-W9.5	APLMK SRB25-W9.5
SRB-2.5(T)-M5/6			MK/SRB-2.5-W9.5	APLMK SRB25-W9.5

* Compliant with RoHS.

* Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.

* Contact JST for details.