



<b>Order code</b>	<b>Manufacturer code</b>	<b>Description</b>
33-1021	n/a	YELLOW 12MM RING TERMINAL PK100 (RC)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

33 1021

Description Data sheet for ERR12, EBR12, EYR12 RING TERMINALS.	Quality system No; DAV2091
---	-------------------------------

Signed: 	ISSUE DATE 23/01/2008	SHEET 2 of 2
---	--------------------------	-----------------



**INSULATED RING TERMINALS**

Working Voltage      600 V. Max AC or DC  
 Working Temperature   -40 To +85 Deg C  
 Basic Tolerance        ±0.5 mm  
 Insulation                Vinyl

For Further Technical Specification  
 Refer To DAV 1069 Sheets 1 To 4

DAVICO PART NO.	STUD SIZE	D (mm)	E (mm)	F (mm)	L (mm)	T (mm)	W (mm)	d1 (mm)	d2 (mm)
ERR12	12mm	4	10	16	35.4	0.75	19.2	1.7	13
EBR12	12mm	4.5	10	16	35.4	0.8	19.2	2.3	13
EYR12	12mm	6.3	13	14.8	37.2	1	18	3.4	13



<b>DAVICO IND LTD</b> KEEPING ELECTRICITY FIRMLY IN IT'S PLACE CHARLES STREET WESTBROMWICH WEST MIDLANDS B70 0AZ	REV 1	DATE		SIG.
	REV 2	DATE		SIG
	REV 3	DATE		SIG
	REV 4	DATE		SIG