




**Accessories for actuator/sensor cables
male flange with strands, rear-mounted
EC-FSFD4.5-0,5/16**



- M12 ⚡ 1 male receptacle
- Protection class IP67
- Rear-mounted
- Connected via stranded wires

Pin Assignment



Type designation	EC-FSFD4.5-0,5/16
Ident no.	6934568
Connector A side	Male receptacle, M12 ⚡ 1, Straight
Number of pins	5
Contacts	Brass, CuZn, Gold-plated
Contact carriers	Plastic, PA GF, Black
Flange housing	Brass, CuZn, nickel-plated
Screw-in thread seal	plastic, NBR
Screw-in thread	M16x1.5
Connection mode	Wire connection
Mechanical lifespan	> 100 Mating cycles
Pollution degree	3
Protection class	IP67, (screwed together)
Cable length	0.5 m
Core insulation	PVC
Core colors	BN, WH, BU, BK, GY
Core cross-section	5x0.34mm ²
Electrical features at +20 °C	
Rated voltage	60 V
Current	4 A
Insulation resistance	≥ 10 ⁸ Ω
Forward resistance	≤ 5 mΩ
Mechanical and chemical properties	
Ambient temperature	
Stationary	-30...+90°C