



Narrow jaw and hinge for delicate work in tight areas. Sharp pointed nose for precise tip cutting. Spring-loaded action for self-opening. Short jaws and beveled cutting edges permit close cutting of wire. Induction-hardened cutting knives for long life. Hot-riveted joint ensures smooth action and no handle wobble. Plastic-dipped handles for comfort and ease of identification. Custom, US-made tool steel.

Specifications

Type:	Narrow-Jaw Midget Pliers	Special Features:	Spring-loaded
Overall Length:	4.25" (108 mm)	Material:	Steel
Nose Type:	Pointed	Jaw Length:	0.5" (12.7 mm)
Jaw Width:	0.406" (10.3 mm)	Jaw Thickness:	1/2" (12.7 mm)
Jaw Capacity:	27/32" (21.4 mm)	Cutting Knives:	Flush
Cut Style:	Flush	Joint Type:	Hot-Riveted
Handle Colour:	Light Blue	Handle Finish:	Plastic-dipped
Handle Length:	3.125" (79.4 mm)	Insulated:	No
Tether capable:	No	Weight:	0.12 lb (0.05 kg)