

PRODUCT-DETAILS

KSU0510

KS FLEX CONDUIT 25MM S/S316 10M



General Information

Extended Product Type	KSU0510
Product ID	7TCA297070R0083
EAN	5011949221741
Catalog Description	KS FLEX CONDUIT 25MM S/S316 10M
Long Description	Very Flexible, Metallic Conduit, Nominal Conduit Size 25mm, 3/4 Inch US Trade Size, Outside Diameter 24.7mm, Inside Diameter 21.1mm, Static Bend Radius 45mm, Reel Length 10 Meters, IP40 Rating, Uncovered Stainless Steel AISI 316L, Metallic

Ordering

EAN	5011949221741
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	5.12 lb 2.322 kg
--------------------	---------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Indoors - Light Industrial, Buildings Marine, Corrosive Environments
Brand / Label	Kopex
Color	Metallic
Flexibility	High
Inside Diameter	21.1 mm
Material	316 Stainless Steel
Nominal Size	3/4 in
Number of Batteries	0
Outside Diameter	24.7 mm
Product Name	flexible metal conduit
Product Type	Flexible, Metallic Conduit
Radius	Static: 45 mm
Special Functions	Contains No Flame Propagating Materials
Standards	BSI Kitemark KM-90009, Low Voltage Directive
UPC	786210277738

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	KSU0510
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	KSU0510

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5539 >> Flexible Metallic Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

