

SC chamfer mill 60°
ULTRA coated



Application

For producing 30° chamfers and for deburring up to 1300 N/mm²

Version

- defined cutting edge rounding
- 6-8 teeth
- High-performance ULTRA coating for universal application

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas- tics	Graphite G(C)FK	GG(G) GjMW	Titan- alloy	Nickel- alloy	Super- alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	110	70	60	80	60	280		170	150	150	130			90	30	30	30	40	35

Art. no.	11541 080
Cutting edge diameter	8 mm
Werkstückkante	30 Grad
Chamfer angle	60 Degree
Type	H
Number of cutting edges	6 PCS
Surface	ULTRA H
Shaft diameter	8 mm
Tool holding device	HB parallel shank
Cutting edge length	8 mm
Suitable for material group P	1
Suitable for material group M	1
Suitable for material group K	1
Suitable for material group N	1
Suitable for material group S	2
Suitable for material group H	1

EAN-Code

4050293743623