

## DCLN steel boring bar, negative left

For facing and longitudinal turning with CN indexable insert

**WIDIA** 

### Application:

For facing and longitudinal turning with CN indexable insert, 80°

### Execution:

- Precision-manufactured steel boring bar, internal cooling, type C, pitch angle 95°, tip angle 80°, clearance angle 0°

### Advantage:

- Universal use for facing and longitudinal turning
- Negative body geometry ensures good stability and absorption of force for large cutting depths



<b>Art. no.</b>	<b>17684 004</b>
<b>Brand</b>	WIDIA
<b>Manufacturer Part Number</b>	5696074
<b>ISO name</b>	A 32 S DCLN R/L 12
<b>Min. bore diameter</b>	40 mm
<b>Shank diameter</b>	32 mm
<b>Length</b>	250 mm
<b>Programming size</b>	22 mm
<b>Suitable for indexable inserts</b>	CN.. 1204..
<b>Tool design</b>	Left
<b>Gross Weight</b>	1.460 kg
<b>Product Group</b>	1XG

### EAN

4050841467568