

<b>Art. no.</b>	<b>50639 310</b>
<b>Model</b>	10
<b>Door design</b>	Perforated plates/slotted plates
<b>Height</b>	1950 mm
<b>Width</b>	1130 mm
<b>Depth</b>	590 mm
<b>Number of shelves, depth 250 mm</b>	6
<b>Number of shelves, depth 530 mm</b>	2
<b>Number of bins 85 x 105 x 45 mm</b>	32
<b>Number of bins 160 x 105 x 75 mm</b>	40
<b>Number of bins 230 x 140 x 130 mm</b>	42
<b>Number of bins 500 x 300 x 200 mm</b>	9
<b>Load-carrying capacity per shelf</b>	50 kg
<b>Load-carrying capacity per drawer</b>	50 kg
<b>Lock type</b>	Cylinder lock
<b>Material</b>	Sheet steel
<b>Body colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Light grey RAL 7035
<b>Surface</b>	Plastic-coated



**EAN-Code**

4251142219263