

## Zubehör für Vollmetallgehäuse

Bezeichnung	Artikelnummer		Maßzeichnung	Maße in mm																																							
<b>Kabelklemme</b> Kabel-Ø ca. 5- 7 mm Kabel-Ø ca. 7-10 mm Kabel-Ø ca. 9-12 mm Kabel-Ø ca. 11-14 mm Kabel-Ø ca. 14-16 mm	für 9-37-polige D-Sub	für 50-polige D-Sub																																									
	61 03 000 0141																																										
	61 03 000 0044																																										
	61 03 000 0143	61 03 000 0145																																									
	61 03 000 0148	61 03 000 0147																																									
<b>Crimpflansch</b>	61 03 000 0062	61 03 000 5062		<table border="1"> <thead> <tr> <th>D1</th> <th>D2</th> </tr> </thead> <tbody> <tr><td>3,0</td><td>4,0</td></tr> <tr><td>3,5</td><td>4,5</td></tr> <tr><td>4,0</td><td>5,0</td></tr> <tr><td>4,5</td><td>5,5</td></tr> <tr><td>5,0</td><td>6,0</td></tr> <tr><td>5,5</td><td>6,5</td></tr> <tr><td>6,0</td><td>7,0</td></tr> <tr><td>6,5</td><td>7,5</td></tr> <tr><td>7,0</td><td>8,0</td></tr> <tr><td>7,5</td><td>8,5</td></tr> <tr><td>8,0</td><td>9,0</td></tr> <tr><td>8,5</td><td>9,5</td></tr> <tr><td>9,0</td><td>10,0</td></tr> </tbody> </table>	D1	D2	3,0	4,0	3,5	4,5	4,0	5,0	4,5	5,5	5,0	6,0	5,5	6,5	6,0	7,0	6,5	7,5	7,0	8,0	7,5	8,5	8,0	9,0	8,5	9,5	9,0	10,0											
	D1	D2																																									
	3,0	4,0																																									
	3,5	4,5																																									
	4,0	5,0																																									
	4,5	5,5																																									
	5,0	6,0																																									
	5,5	6,5																																									
	6,0	7,0																																									
	6,5	7,5																																									
	7,0	8,0																																									
	7,5	8,5																																									
	8,0	9,0																																									
	8,5	9,5																																									
	9,0	10,0																																									
61 03 000 0063	61 03 000 5063																																										
61 03 000 0064	61 03 000 5064																																										
61 03 000 0065	61 03 000 5065																																										
61 03 000 0066	61 03 000 5066																																										
61 03 000 0166	61 03 000 5166																																										
61 03 000 0067	61 03 000 5067																																										
61 03 000 0068	61 03 000 5068																																										
61 03 000 0069	61 03 000 5069																																										
61 03 000 0070	61 03 000 5070																																										
61 03 000 0071	61 03 000 5071																																										
61 03 000 0165	61 03 000 5165																																										
61 03 000 0072	61 03 000 5072																																										
<b>Crimphülse</b>	61 03 000 0045	<table border="1"> <thead> <tr> <th>D3</th> <th>D4</th> </tr> </thead> <tbody> <tr><td>5,0</td><td>6,0</td></tr> <tr><td>5,5</td><td>6,5</td></tr> <tr><td>6,0</td><td>7,0</td></tr> <tr><td>6,5</td><td>7,5</td></tr> <tr><td>7,0</td><td>8,0</td></tr> <tr><td>7,5</td><td>8,5</td></tr> <tr><td>8,0</td><td>9,0</td></tr> <tr><td>8,5</td><td>9,5</td></tr> <tr><td>9,0</td><td>10,0</td></tr> <tr><td>9,5</td><td>10,5</td></tr> <tr><td>10,0</td><td>11,0</td></tr> <tr><td>10,5</td><td>11,5</td></tr> <tr><td>11,0</td><td>12,0</td></tr> <tr><td>11,5</td><td>12,5</td></tr> <tr><td>12,0</td><td>13,0</td></tr> <tr><td>12,5</td><td>13,5</td></tr> <tr><td>13,0</td><td>14,0</td></tr> <tr><td>13,7</td><td>15,0</td></tr> <tr><td>14,0</td><td>15,0</td></tr> </tbody> </table>	D3	D4	5,0	6,0	5,5	6,5	6,0	7,0	6,5	7,5	7,0	8,0	7,5	8,5	8,0	9,0	8,5	9,5	9,0	10,0	9,5	10,5	10,0	11,0	10,5	11,5	11,0	12,0	11,5	12,5	12,0	13,0	12,5	13,5	13,0	14,0	13,7	15,0	14,0	15,0	
	D3		D4																																								
	5,0		6,0																																								
	5,5		6,5																																								
	6,0		7,0																																								
	6,5		7,5																																								
	7,0		8,0																																								
	7,5		8,5																																								
	8,0		9,0																																								
	8,5		9,5																																								
	9,0		10,0																																								
	9,5		10,5																																								
	10,0		11,0																																								
	10,5		11,5																																								
	11,0		12,0																																								
	11,5		12,5																																								
	12,0		13,0																																								
	12,5		13,5																																								
	13,0		14,0																																								
	13,7		15,0																																								
14,0	15,0																																										
61 03 000 0046																																											
61 03 000 0047																																											
61 03 000 0048																																											
61 03 000 0049																																											
61 03 000 0050																																											
61 03 000 0051																																											
61 03 000 0052																																											
61 03 000 0053																																											
61 03 000 0054																																											
61 03 000 0055																																											
61 03 000 0056																																											
61 03 000 0057																																											
61 03 000 0058																																											
61 03 000 0142																																											
61 03 000 0059																																											
61 03 000 0127																																											
61 03 000 0060																																											
61 03 000 0061																																											
<b>Blindstopfen für Gehäuse</b>	61 03 000 0042	61 03 000 0041																																									
<b>Inbusschraube</b> Gewinde 4-40 UNC x 17,5-8.8 mit Federring Gewinde M3 x 17,5-8.8 mit Federring	09 67 002 9020																																										
	09 67 002 9019																																										
<b>Rändelschraube</b> Gewinde 4-40 UNC Gewinde M3	09 67 002 9018																																										
	09 67 002 9017																																										

D-Sub