


C87, Film, Film/Foil Polypropylene, Motor Run, 70 uF, 5%, 470 VAC



General Information	
Supplier:	KEMET
Series:	C87
Dielectric:	Film/Foil Polypropylene
Style:	Can
Description:	Aluminum Case, Plastic Cover, Spun Seal
Features:	Spun Seal, Safety Class S2, UL_94 V0 Disk
RoHS:	Yes
Lead:	Fast On (2+2)
Qualifications:	UL, VDE, CQC, CSA (600VAC), UL_94 V0 Disk

Dimensions	
D	55mm +1mm
L	133mm +/-2mm

Specifications	
Capacitance:	70 uF
Capacitance Tolerance:	5%
Voltage AC:	470 VAC
Temperature Range:	-25/+85C
Rated Temperature:	85°C
Max dV/dt:	15 V/us

Packaging Specifications	
Mounting:	Bolt - M12x12.5
Packaging:	Bulk, Bag
Packaging Quantity:	32

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.